

Flat suction cup (round)

SPF 50 ED-65 G1/4-AG

Part no.: 10.01.01.13248

<https://www.schmalz.com/10.01.01.13248>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Flat Suction Cups SPF > SPF 50 ED-65 G1/4-AG

Flat suction cup (round) for dynamic handling of cardboard and rigid packaging




Size: 50

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Design Data



Attribute	Value
dn	6.10 mm
Dmax(S)	53.90 mm
Ds	51.40 mm
G1	G1/4"-M
H	23.20 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	3.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	74.20 N
Pull-off force	87.40 N
Lateral force	44 N
Volume	7.96 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Size	50

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (round)

SPF 50 ED-65 G1/4-AG

Part no.:10.01.01.13248

<https://www.schmalz.com/10.01.01.13248>

Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	20.10 g
Product family	SPF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SIEB 17.5x0.8 MS-A2 280 0.28/0.16

Part no.:10.07.01.00308

External diameter D: 17.5 mm

Length L: 0.8 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm



SU 50

Part no.:10.01.01.12837

Size: 50

Clamping range: 45.0 ... 60.0 mm

Temperature resistance: 80 °C

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (round)

SPF 50 ED-65 G1/4-AG

Part no...:10.01.01.13248

<https://www.schmalz.com/10.01.01.13248>



SC-SW 60 6

Part no...:10.05.04.00096

Spanner size SW1: 6 mm

Nominal size: 60



SC-SW 80 6

Part no...:10.05.04.00097

Spanner size SW1: 6 mm

Nominal size: 80



SC-SW 100 6

Part no...:10.05.04.00098

Spanner size SW1: 6 mm

Nominal size: 100

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (round)

SPF 50 ED-65 G1/4-AG

Part no...:10.01.01.13248

<https://www.schmalz.com/10.01.01.13248>



SC-SW 120 6

Part no...:10.05.04.00099

Spanner size SW1: 6 mm

Nominal size: 120



SC-SW 200 6

Part no...:10.05.04.00100

Spanner size SW1: 6 mm

Nominal size: 200



SC-SW 240 6

Part no...:10.05.04.00101

Spanner size SW1: 6 mm

Nominal size: 240

Spare parts

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (round)

SPF 50 ED-65 G1/4-AG

Part no...:10.01.01.13248

<https://www.schmalz.com/10.01.01.13248>



SC 050 G1/4-AG MOD

Part no...:10.01.06.02487

Connection geometry: 050

Connection: G1/4"-M

Length L1: 26.5 mm

Fitting length: 7.2 mm

Nominal diameter dn: 6.1 mm



SPF 50 ED-65 SC050

Part no...:10.01.01.12374

Size: 50

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Height H: 16 mm

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es