

Flat suction cup (oval)

SGON 15x5 SI-HD-65 M5-IG

Part no...:10.01.05.01047

<https://www.schmalz.com/10.01.05.01047>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON > SGON 15x5 SI-HD-65 M5-IG

Flat suction cup (oval) for long and also curved workpieces




Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Nipple material: Aluminum

Connection: M5-F

Design Data



Attribute	Value
Bmax(S)	5.50 mm
Bs	5 mm
dn	1.20 mm
G1	M5-F
H	22 mm
LG1	5.50 mm
Lmax(S)	15.50 mm
Ls	15 mm
SW1	8 mm
Z (Stroke)	0.70 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	3.10 N
Volume	0.18 cm ³
Curve radius (min) (convex)	4 mm
Hose diameter (rec.) d	2 mm
Number of folds	0
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (oval)

SGON 15x5 SI-HD-65 M5-IG

Part no.:10.01.05.01047

<https://www.schmalz.com/10.01.05.01047>

Weight	3.50 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SGO 15x5 SI-HD-65 N021

Part no.:10.01.05.01028

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A



SA-NIP N021 M5-IG DN200

Part no.:10.01.05.00125

Thread G1: M5-F

Length L1: 15.5 mm

Fitting length: 10 mm

Nominal diameter dn: 2 mm

Material: Aluminum

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es