

Flat suction cup (oval)

SGON 75x25 SI-HD-65 G1/4-AG

Part no.:10.01.05.01060

<https://www.schmalz.com/10.01.05.01060>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON > SGON 75x25 SI-HD-65 G1/4-AG

Flat suction cup (oval) for long and also curved workpieces




Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Nipple material: Aluminum

Connection: G1/4"-M

Design Data



Attribute	Value
Bmax(S)	27.50 mm
Bs	24 mm
dn	3.50 mm
G1	G1/4"-M
H	26 mm
LG1	10 mm
Lmax(S)	77 mm
Ls	74 mm
SW1	17 mm
Z (Stroke)	2.80 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	78.30 N
Volume	5.86 cm ³
Curve radius (min) (convex)	30 mm
Hose diameter (rec.) d	6 mm
Number of folds	0
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (oval)

SGON 75x25 SI-HD-65 G1/4-AG

Part no.:10.01.05.01060

<https://www.schmalz.com/10.01.05.01060>

Weight	26.90 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SGO 75x25 SI-HD-65 N023

Part no.:10.01.05.01040

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A



SA-NIP N023 G1/4-AG DN350

Part no.:10.01.05.00122

Thread G1: G1/4"-M

Length L1: 25 mm

Fitting length: 5 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (oval)

SGON 75x25 SI-HD-65 G1/4-AG

Part no...:10.01.05.01060

<https://www.schmalz.com/10.01.05.01060>



SA-NIP N023 G1/4-IG DN350

Part no...:10.01.05.00121

Thread G1: G1/4"-F

Length L1: 25 mm

Fitting length: 15 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



ZOKL 15-18

Part no...:10.07.10.00033

Clamping range: 15.0 ... 18.0 mm

Material: Galvanized steel

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es