

## Glass-Cup

ISCUP-G 80x80x30 Cup 1

Part no...:10.01.15.00392

<https://www.schmalz.com/10.01.15.00392>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP-G 80x80x30 Cup 1

### Suction Glas-cup for Innospann



Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm

### Design Data



| Attribute | Value |
|-----------|-------|
| B         | 80 mm |
| H         | 30 mm |
| L         | 80 mm |

### Technical Data

| Attribute | Value   |
|-----------|---------|
| Weight    | 0.17 kg |

### Spare parts

#### Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | [schmalz@schmalz.es](mailto:schmalz@schmalz.es)

## Glass-Cup

ISCUP-G 80x80x30 Cup 1

Part no...:10.01.15.00392

<https://www.schmalz.com/10.01.15.00392>



### DI-PROF 4x10 MOS EPDM HR

Part no...:10.01.15.00062

Width B: 4 mm

Height H: 10 mm

Sealing material: EPDM

Material type: Foam rubber

Form: half-round



### ISDR 81x81x12 Cup 1 NBR-50

Part no...:10.01.15.00158

Length L: 81 mm

Width B: 81 mm

Height H: 12 mm

## Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | [schmalz@schmalz.es](mailto:schmalz@schmalz.es)