

Cup

ISCUP Cup 4 100x100x30 TV

Part no...:10.01.15.00405

<https://www.schmalz.com/10.01.15.00405>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP Cup 4 100x100x30 TV

Suction cup for Innospann



Dimensions (LxB): 100 x 100


Length L: 100 mm

Width B: 100 mm

Height H: 30 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	100 mm
d	60 mm
H	30 mm
L	100 mm

Technical Data

Attribute	Value
Weight	0.20 kg

Spare parts

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Cup

ISCUP Cup 4 100x100x30 TV

Part no...:10.01.15.00405

<https://www.schmalz.com/10.01.15.00405>



DI-PROF 4x10 MOS EPDM HR

Part no...:10.01.15.00062


Width B: 4 mm

Height H: 10 mm

Sealing material: EPDM

Material type: Foam rubber

Form: half-round



ISDR 100x100x12 Cup 4


Part no...:10.01.15.00404

Width B: 100 mm

Height H: 12 mm

Length L: 100 mm

Type: Cup 4



ISRPL 86x86x8.7 NBR-55 d5

Part no...:10.01.15.00402

Width B: 86 mm

Internal diameter d: 5 mm

Height H: 8.7 mm

Length L: 86 mm

Suction cup material: Nitrile rubber NBR-55

Type: CUP 100

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Cup

ISCUP Cup 4 100x100x30 TV

Part no...:10.01.15.00405

<https://www.schmalz.com/10.01.15.00405>



O-RING 48x2 CR-70

Part no...:10.07.08.00468



TV D11 4.3

Part no...:10.01.15.00347

External diameter D: 11 mm

Spring stroke Z: 4.3 mm

Length L: 24 mm