

Ejector module

SEP HV 2 16 22 S

Part no.:10.02.01.01410

<https://www.schmalz.com/10.02.01.01410>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Ejector Modules > Ejector Modules ecoPump SEP > SEP HV 2 16 22 S

Multistagenozzle as a cartridge



Shape: High Vacuum

Number of stages: 2

Nozzle size: 1.6 mm

Hole diameter: 22 mm

construction shape compact ejectors: With safety valve

Degree of evacuation: 90 %


Pressure range (operating pressure): 2.0 ... 6.0 bar

Pressure optimal: 4 bar

Suction rate (max.): 137.3 l/min

Air consumption suction: 103 l/min

Design Data



Attribute	Value
D1	10.80 mm
D2	21.80 mm
L1	8 mm
L2	67.50 mm
L3	92 mm

Technical Data

Attribute	Value
Weight	15.80 g
Operating temperature	0 ... 60 °C
Recomm. internal hose diameter compressed air	6 mm
Recomm. internal hose diameter vacuum	12 mm
Pressure range (operating pressure)	2.0 ... 6.0 bar
Pressure range (operating pressure)	29.0 ... 87.0
Pressure optimal	4 bar
Pressure optimal	58 psi

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Ejector module

SEP HV 2 16 22 S

Part no...:10.02.01.01410

<https://www.schmalz.com/10.02.01.01410>

Sound level free	87 dB(A)
Sound level suction	76 dB(A)
construction shape compact ejectors	S
Suction rate (max.)	8.20 m³/h
Suction rate (max.)	137.30 l/min
Suction rate (max.)	4.85 cfm
Air consumption suction	6.34 m³/h
Air consumption suction	103 l/min
Air consumption suction	3.64 cfm
Degree of evacuation	90 %
Number of stages	2
Nozzle size	1.60 mm
Hole diameter	22 mm
Shape	High Vacuum
Product family	SEP

Accessories



SHC 2 22

Part no...:10.02.01.01512

Number of stages: 2

Hole diameter: 22 mm

External diameter D: 20 mm

Length L: 33 mm

Thread G1: M27x1.5-M

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Ejector module

SEP HV 2 16 22 S

Part no...:10.02.01.01410

<https://www.schmalz.com/10.02.01.01410>



SD 29x70 SHC 22

Part no...:10.02.01.01517

External diameter D: 29 mm

Length L: 70 mm

Construction use: Schmalz Holder Cap

Size: 22



SFE 22 AL

Part no...:10.02.01.01421

Hole diameter: 22 mm

Width B: 35 mm

Height H: 44 mm

Length L: 87.5 mm

Thread G1: G1/4"-F

Thread G2: G3/8"-F

Compressed-air connection: G1/4"-F

Suction cup connection: G3/8"-F

Vacuum connection: G1/4"-F



SFE 22 POM

Part no...:10.02.01.01767

Hole diameter: 22 mm

Width B: 31.5 mm

Height H: 45 mm

Length L: 80 mm

Thread G1: G1/4"-F

Thread G2: G3/8"-F

Compressed-air connection: G1/4"-F

Suction cup connection: G3/8"-F

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Ejector module

SEP HV 2 16 22 S

Part no...:10.02.01.01410

<https://www.schmalz.com/10.02.01.01410>



BEF-WIN 50x40x41 5 SFE-22

Part no...:10.08.03.00315

Width B: 50 mm

Height H: 40 mm

Length L: 41 mm

Construction use: Schmalz Fixation Element

Size: 22



SET SFE 22

Part no...:10.02.01.01577

Width B: 20 mm

Height H: 20 mm

Length L: 27 mm

Construction use: Schmalz Fixation Element

Size: 22

Thread G1: G1/4"-M

Thread G2: M8-M



SEV G1/8-IG G1/4-AG

Part no...:10.02.01.01471

External diameter D: 19 mm

Length L: 37 mm

Thread G1: G1/8"-F

Thread G2: G1/4"-M

Spare parts

Contact Schmalz


Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Ejector module

SEP HV 2 16 22 S

Part no...:10.02.01.01410

<https://www.schmalz.com/10.02.01.01410>



ERS SEP-22 6xRUE-KLAP

Part no...:10.02.01.01450

Construction use: Ejector module

Size: 22

contains: 6x flap

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es