

Vacuum centre

VZ-TR 25 AC3 50

Part no.:10.03.04.00136

<https://www.schmalz.com/10.03.04.00136>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Centers > Vacuum Centers VZ > VZ-TR 25 AC3 50

Vacuum centre with oil-free pump and vacuum reservoir




Suction rate: 25 m³/h

Voltage: 230/400 V, 50 Hz

Reservoirs volume: 50 l

Design Data



Attribute	Value
B	510 mm
B1	630 mm
d	11 mm
G2	G1-1/4-F
H	580 mm
L	710 mm
L1	730 mm
X1	480 mm
Y1	470 mm

Technical Data

Attribute	Value
Max. vacuum	-850 mbar
Voltage	230/400 V, 50 Hz
Motor power	0.75 kW
Reservoirs volume	50 l
Suction rate	25 m ³ /h
Protection type IP	IP 54
Weight	69 kg
Max. vacuum	-25.10 inHg

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Vacuum centre

VZ-TR 25 AC3 50

Part no.:10.03.04.00136

<https://www.schmalz.com/10.03.04.00136>

Product family

VZ

Spare parts



FILT-EINS EVE-TR-25-40

Part no.:10.03.01.00023

Size: 25-40

Construction use: Pump EVE-TR



FILT-EINS 3 98x70 PAP STF-1-1/4-IGN

Part no.:10.07.01.00018

Filter pore size: 3 µm

External diameter D: 98 mm

Length L: 70 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 1-1/4-IGN

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es