

Vacuum centre

VZ-TR 10 AC3 15 GMS

Part no...:10.03.04.00173

<https://www.schmalz.com/10.03.04.00173>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Centers > Vacuum Centers VZ > VZ-TR 10 AC3 15 GMS

Vacuum centre with oil-free pump and vacuum reservoir




Suction rate: 10 m³/h

Voltage: 230/400V ±10%

Reservoirs volume: 15 l

with: Regulated engine circuit

Design Data



Attribute	Value
B	400 mm
B1	490 mm
d	11 mm
G2	G3/4"-F
H	440 mm
L	430 mm
L1	430 mm
X1	280 mm
Y1	360 mm

Technical Data

Attribute	Value
Max. vacuum	-850 mbar
Voltage	230/400V ±10%
Motor power	0.37 kW
Reservoirs volume	15 l
Suction rate	10 m ³ /h
Protection type IP	IP 44
Weight	38.50 kg
Max. vacuum	-25.10 inHg

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Vacuum centre

VZ-TR 10 AC3 15 GMS

Part no.:10.03.04.00173

<https://www.schmalz.com/10.03.04.00173>

Product family

VZ

Spare parts



FILT-EINS 3 65x70 PAP STF-3/4-IG

Part no.:10.07.01.00017

Filter pore size: 3 µm

External diameter D: 65 mm

Length L: 69.5 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 3/4-IG



FILT-EINS EVE-16-25

Part no.:10.03.01.00022

Size: 16-25

Construction use: Pump EVE

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es