

Plug union, straight

STV-GE G1/8-AG 8

Part no.:10.08.02.00206

<https://www.schmalz.com/10.08.02.00206>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-GE G1/8-AG 8

Push-in Fitting, straight



Thread G1: G1/8"-M

Hose diameter: 8 mm


Material: Brass

Operating temperature: °C

External diameter D: 14 mm

Length L: 20.7 mm

Design Data



Attribute	Value
D	14 mm
d	8 mm
G1	G1/8"-M
dn	5.10 mm
L	20.70 mm
L1	26.20 mm
L2	16.40 mm
LG1	5.50 mm
SW1	14 mm

Technical Data

Attribute	Value
Hose type	Hose D = 8 d = 6
Hose type	8-6
Material	Brass
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	16.30 g
Product family	STV

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es


Plug union, straight

STV-GE G1/8-AG 8

Part no.:10.08.02.00206

<https://www.schmalz.com/10.08.02.00206>

Accessories



VSL 8-6 PE BL

Part no.:10.07.09.00015

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es