

Flat suction cup (round)

PFG 15 PU-55 N005

Part no.:10.01.01.00051

<https://www.schmalz.com/10.01.01.00051>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 15 PU-55 N005

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 15

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	4.50 mm
d1	7.80 mm
Dk	12.20 mm
Dmax(S)	17.50 mm
Ds	15 mm
H	8 mm
H2	2.60 mm
Z (Stroke)	1.90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	9 N
Volume	0.43 cm ³
Curve radius (min) (convex)	12.50 mm
Size	15
Nipple family	N 005
Suction cup material	Polyurethane PU
Material hardness [Shore A]	55 Shore A
Weight	0.70 g

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (round)

PFG 15 PU-55 N005

Part no.:10.01.01.00051

<https://www.schmalz.com/10.01.01.00051>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N005 G1/8-AG DN200

Part no.:10.01.01.03529

Nipple family: N 005

Thread G1: G1/8"-M

Length L1: 17.5 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2 mm

Material: Aluminum



SA-NIP N005 G1/8-IG DN200

Part no.:10.01.01.03521

Nipple family: N 005

Thread G1: G1/8"-F

Length L1: 20.5 mm

Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 2 mm

Material: Aluminum

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es