

Suction cup cover

SU 40

Part no...:10.01.01.12856

<https://www.schmalz.com/10.01.01.12856>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Accessories Vacuum Suction Cups > Suction Cup Covers SU > SU 40

Cover for suction cup



Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C

Design Data



Attribute	Value
d	5 mm
D	47 mm
D2	30 mm

Technical Data

Attribute	Value
Size	40
Clamping range	35.0 ... 45.0 mm
Weight	0.50 g
Product family	SU

Note: In vertical applications with a suction plate or cup, the lateral force sinks by up to 70%. The vacuum generator must be able to provide 10% more suction power

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es