

Hose clamp

SSB 20-32 ST-VZ

Part no.:10.07.10.00003

<https://www.schmalz.com/10.07.10.00003>

Home > Vacuum Lifters and Crane Systems > Vacuum Tube Lifters Jumbo > Spare Parts Vacuum Tube Lifters Jumbo > Spare and Wear Parts Vacuum Tube Lifters JumboFlex > SSB 20-32 ST-VZ

Hose clamp for securing smooth hoses




Clamping range: 20.0 ... 32.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	20 mm
d2	32 mm
L	9 mm

Technical Data

Attribute	Value
Clamping range	20.0 ... 32.0 mm
Material	Steel
Weight	16 g
Product family	SSB / SSD

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Hose clamp

SSB 20-32 ST-VZ

Part no.:10.07.10.00003

<https://www.schmalz.com/10.07.10.00003>

Accessories



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



VSL 21-12 PVC-G KL-TR

Part no.:10.07.09.00006

External diameter D: 21 mm

Internal diameter d: 12 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 26-19 PVC-DS KL-TR

Part no.:10.07.09.00007

External diameter D: 26 mm

Internal diameter d: 19 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es