

Vacuum block


VCBL-R 110x110x45 30x30 TV

Part no...:10.01.12.02883

<https://www.schmalz.com/10.01.12.02883>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Grid Table Systems > Vacuum block
VCBL-R > VCBL-R 110x110x45 30x30 TV

Vacuum block for grid tables



Dimensions (LxB): 110 x 110

Length L: 110 mm

Width B: 110 mm


Height H: 45 mm

Grid: 30x30

Recommended slot width x slot depth [mm]: 6,4x6,1 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	110 mm
H	45 mm
L	110 mm

Technical Data

Attribute	Value
Grid	30x30
Weight	0.98 kg

Spare parts

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Vacuum block

VCBL-R 110x110x45 30x30 TV

Part no...:10.01.12.02883

<https://www.schmalz.com/10.01.12.02883>



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



ERS VCBL-R Winkel

Part no...:10.01.12.02691



ERS VCBL-R

Part no...:10.01.12.02693

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Vacuum block

VCBL-R 110x110x45 30x30 TV

Part no...:10.01.12.02883

<https://www.schmalz.com/10.01.12.02883>



DI-PROF 4x6 MOS NK-20 HR

Part no...:10.07.04.00054

Width B: 4 mm

Height H: 6 mm

Material type: Foam rubber

Sealing material: Natural Rubber NK

Material hardness [Shore A]: 20 Shore A

Form: half-round

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es