

## Bellows suction cup (round)

FG 62 NK-45 N018

Part no.:10.01.06.00459

<https://www.schmalz.com/10.01.06.00459>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 62 NK-45 N018

### Bellows suction cup (round) for very uneven workpieces




Size: 62

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Number of folds: 2.5

### Design Data



| Attribute  | Value    |
|------------|----------|
| d          | 8 mm     |
| d2         | 29.50 mm |
| D1         | 62 mm    |
| Dk         | 18 mm    |
| Dmax(S)    | 65 mm    |
| Ds         | 62.20 mm |
| H          | 54 mm    |
| H2         | 13 mm    |
| Z (Stroke) | 29 mm    |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                   | Value                 |
|-----------------------------|-----------------------|
| Suction force (-600mbar)    | 41.01 N               |
| Pull-off force              | 137 N                 |
| Volume                      | 61.12 cm <sup>3</sup> |
| Curve radius (min) (convex) | 75 mm                 |
| Size                        | 62                    |
| Nipple family               | N 018                 |
| Number of folds             | 2.50                  |
| Suction cup material        | Natural Rubber NK     |

### Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | [schmalz@schmalz.es](mailto:schmalz@schmalz.es)

## Bellows suction cup (round)

FG 62 NK-45 N018

Part no.:10.01.06.00459

<https://www.schmalz.com/10.01.06.00459>

|                             |            |
|-----------------------------|------------|
| Material hardness [Shore A] | 45 Shore A |
| Weight                      | 52 g       |
| Product family              | FG         |

### Accessories



#### SA-NIP N018 G1/4-AG DN440

Part no.:10.01.06.01065

Nipple family: N 018

Thread G1: G1/4"-M

Length L1: 28.8 mm

Fitting length: 4 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum



#### SA-NIP N018 G1/4-IG DN440

Part no.:10.01.06.01066

Nipple family: N 018

Thread G1: G1/4"-F

Length L1: 28.8 mm

Fitting length: 15 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum

### Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | [schmalz@schmalz.es](mailto:schmalz@schmalz.es)