

Flat suction cup (oval)

SGO 24x8 NBR-CO-55 N022

Part no.:10.01.05.00739

<https://www.schmalz.com/10.01.05.00739>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 24x8 NBR-CO-55 N022

Flat suction cup (oval) for narrow or curved workpieces




Dimensions (LxB): 24 x 8

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
Bmax(S)	9 mm
Bs	7.60 mm
d	5.50 mm
d1	7 mm
dn	1.50 mm
Dk	11.50 mm
Lmax(S)	24.50 mm
Ls	23.60 mm
H	12 mm
H2	3 mm
H3	5.50 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	8 N
Dimensions (LxB)	24 x 8
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A
Weight	1 g

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es



Flat suction cup (oval)

SGO 24x8 NBR-CO-55 N022

Part no...:10.01.05.00739

<https://www.schmalz.com/10.01.05.00739>

Product family

SGO

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Page 2 from 2