

Sealing cord

DI-SCHN 10 MOS EPDM-20

Part no...:10.07.04.00003

<https://www.schmalz.com/10.07.04.00003>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Sealing Profiles > Sealing Cords DI-SCHN > DI-SCHN 10 MOS EPDM-20

Sealing cord




External diameter D: 10 mm

Material type: Foam rubber

Sealing material: EPDM

Material hardness [Shore A]: 20 Shore A

Design Data



Attribute	Value
D	10 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Technical Data

Attribute	Value
Min. bending radius	10 mm
Product family	DI-SCHN

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es