

Flat suction cup (round)

SGAN 7 PU-60 M5-IG

Part no.:10.01.01.00799

<https://www.schmalz.com/10.01.01.00799>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > Flat Suction Cups SGAN > SGAN 7 PU-60 M5-IG

Flat suction cup (round) for particularly sensitive workpieces




Size: 7

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 60 Shore A

Connection: M5-F

Design Data



Attribute	Value
dn	2 mm
Dmax(S)	7.50 mm
Ds	7 mm
G1	M5-F
H	22 mm
LG1	5.50 mm
SW1	8 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1.60 N
Volume	0.19 cm ³
Curve radius (min) (convex)	7.50 mm
Hose diameter (rec.) d	2 mm
Size	7
Nipple family	N 028
Suction cup material	Polyurethane PU

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (round)

SGAN 7 PU-60 M5-IG

Part no.:10.01.01.00799

<https://www.schmalz.com/10.01.01.00799>

Material hardness [Shore A]	60 Shore A
Weight	1.70 g
Number of folds	0
Product family	SGAN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N028 M5-IG DN200

Part no.:10.01.01.00813

Thread G1: M5-F

Fitting length: 10 mm

Material: Aluminum



SGA 7 PU-55 N028

Part no.:10.01.01.00570

Size: 7

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es