

Bell suction cup (round)

SAG 80 NBR-60 G1/4-IG

Part no.:10.01.01.12268

<https://www.schmalz.com/10.01.01.12268>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAG > SAG 80 NBR-60 G1/4-IG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 80


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/4-IG

Design Data



Attribute	Value
dn	6 mm
Dmax(S)	90.70 mm
Ds	83 mm
G1	G1/4"-F
H	40 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	12.80 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	217 N
Lateral force	284 N
Lateral force (oily surface)	167 N
Volume	44 cm ³
Curve radius (min) (convex)	70 mm
Hose diameter (rec.) d	6 mm
Size	80
Suction cup material	Nitrile rubber NBR

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Bell suction cup (round)

SAG 80 NBR-60 G1/4-IG

Part no...:10.01.01.12268

<https://www.schmalz.com/10.01.01.12268>

Material hardness [Shore A]	60 Shore A
Number of folds	0
Weight	59.10 g
Product family	SAG