

Bell suction cup (oval)

SAOXM 60x20 ED-85 SC045-AR

Part no.:10.01.24.00001

<https://www.schmalz.com/10.01.24.00001>

High-Speed bell shaped suction cup




Dimensions (LxB): 60 x 20

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Design Data



Attribute	Value
Bk	20 mm
Bmax(S)	24 mm
Bs	18.70 mm
d	12.80 mm
H	21.90 mm
H2	3 mm
Lk	60 mm
Ls	61.80 mm
Z (Stroke)	4.50 mm

Technical Data

Attribute	Value
Lateral force	44 N
Lateral force (oily surface)	62 N
Volume	5 cm ³
Curve radius (min) (convex)	10 mm
Hose diameter (rec.) d	4 mm
Nipple family	SC 045-AR
Dimensions (LxB)	60 x 20
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es



Bell suction cup (oval)

SAOXM 60x20 ED-85 SC045-AR

Part no...:10.01.24.00001

<https://www.schmalz.com/10.01.24.00001>

Weight	7.20 g
Number of folds	0
Product family	SAOXM

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Page 2 from 2