

Flat suction cup (round)

SGPN 34 FPM-65 G1/4-AG

Part no.:10.01.01.12920

<https://www.schmalz.com/10.01.01.12920>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Flat Suction Cups SGPN > SGPN 34 FPM-65 G1/4-AG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 34

Suction cup material: Fluorocaotchuc FPM

Material hardness [Shore A]: 65 Shore A

Nipple material: Aluminum

Vacuum connection: G1/4"-M

Design Data



Attribute	Value
dn	5.50 mm
Dmax(S)	37.50 mm
Ds	34 mm
G1	G1/4"-M
H	28 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	2.20 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	25 N
Volume	3.70 cm ³
Hose diameter (rec.) d	4 mm
Size	34
Number of folds	0
Suction cup material	Fluorocaotchuc FPM
Material hardness [Shore A]	65 Shore A

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SGPN 34 FPM-65 G1/4-AG

Part no.:10.01.01.12920

<https://www.schmalz.com/10.01.01.12920>

Weight	14.60 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N033 G1/4-AG DN550

Part no.:10.01.01.00818

Thread G1: G1/4"-M

Fitting length: 5 mm

Material: Aluminum



SGP 34 FPM-65 N033

Part no.:10.01.01.12919

Size: 34

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A