

Flat suction cup (round)

SFF 30 EPDM-45 SC040

Part no.:10.01.01.14048

<https://www.schmalz.com/10.01.01.14048>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > SFF 30 EPDM-45 SC040

Flat suction cups (round) for the gentle handling of thin and flexible workpieces




Size: 30

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Number of folds: 0

Design Data



Attribute	Value
Dmax(S)	31.50 mm
Dk	14.80 mm
Ds	30 mm
d	7.50 mm
d1	10.40 mm
H	13.50 mm
H2	4.70 mm
H3	6.80 mm
Z (Stroke)	2 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	26.90 N
Volume	1.67 cm ³
Size	30
Number of folds	0
Suction cup material	EPDM
Material hardness [Shore A]	45 Shore A
Curve radius (min) (convex)	30 mm
Nipple family	SC 040

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SFF 30 EPDM-45 SC040

Part no.:10.01.01.14048

<https://www.schmalz.com/10.01.01.14048>

Weight	2.50 g
Product family	SFF

Accessories



SC 040 G1/4-AG

Art-Nr.:10.01.06.03414

Connection geometry: 040

Vacuum connection: G1/4"-M

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm



SC 040 G1/4-IG

Art-Nr.:10.01.06.02918

Connection geometry: 040

Vacuum connection: G1/4"-F

Fitting length: 17.3 mm

Nominal diameter dn: 4.1 mm

Ersatzteile

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SFF 30 EPDM-45 SC040

Part no.:10.01.01.14048

<https://www.schmalz.com/10.01.01.14048>



SC 040 M5-AG

Art-Nr.:10.01.06.04346

Connection geometry: 040

Vacuum connection: M5-M

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm