

Flat suction cup (round)

SUF 25 NBR-55 G1/8-AG

Part no.:10.01.01.14116

<https://www.schmalz.com/10.01.01.14116>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 25 NBR-55 G1/8-AG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces




Size: 25

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
Dmax(S)	28.20 mm
Ds	25 mm
dn	4.10 mm
G1	G1/8"-M
H	17.20 mm
LG1	7.50 mm
SW1	14 mm
Z (Stroke)	2.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	23 N
Pull-off force	23 N
Volume	0.90 cm ³
Curve radius (min) (convex)	25 mm
Hose diameter (rec.) d	4 mm
Size	25
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SUF 25 NBR-55 G1/8-AG

Part no.:10.01.01.14116

<https://www.schmalz.com/10.01.01.14116>

Weight	9.70 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC 040 G1/8-AG

Part no.:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20.2 mm

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm



SUF 25 NBR-55 SC040

Part no.:10.01.01.13948

Size: 25

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A