

Compact ejector

SCP 30 FS

Part no...:10.02.02.00908

<https://www.schmalz.com/10.02.02.00908>




Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Compact Ejectors > Compact Ejectors SCP-FS > SCP 30 FS

Compact ejector with integrated functions



- Nozzle diameter: 3 mm
- Suction rate (max.): 200 l/min
- Air consumption suction: 420 l/min
- Pressure range (operating pressure): 5.0 ... 6.0 bar
- Control valve: External control

Design Data



Attribute	Value
B	22 mm
d	5.50 mm
G1	G1/4"-F
G2	G3/8"-F
H	54 mm
H1	127.50 mm
H2	73.50 mm
H3	20.10 mm
L	112.50 mm
L2	37.50 mm
X1	49.50 mm
X2	69.50 mm
Y1	12 mm

Technical Data

Attribute	Value
Nozzle diameter	3 mm
Degree of evacuation	85 %
Suction rate (max.)	200 l/min
Control valve	External control

Compact ejector

SCP 30 FS

Part no...:10.02.02.00908

<https://www.schmalz.com/10.02.02.00908>

Suction rate (max.)	7.06 cfm
Product family	SCP

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Spare parts



FILT-EINS 50 14x49 PE-POR SCP-SMP

Part no...:10.02.02.00654

External diameter D: 13.6 mm
Length L: 48.5 mm
Filter material: Polyethylene
Construction use: Compact ejectors



SD 50.5x21x68.5 SMP/SCP25/30

Part no...:10.02.02.00652

Length L: 50.5 mm
Width B: 21 mm
Height H: 68.5 mm
Construction use: Compact ejectors SMP/SCP