

Solenoid valve

EMVO 20 230V-AC 3/2 NC

Part no.:10.05.01.00053

<https://www.schmalz.com/10.05.01.00053>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMVO > EMVO 20 230V-AC 3/2 NC

Solenoid valve EMVO for direct control of vacuum



Nominal size: 20 mm


Voltage DC: 230V - AC

Function: 3/2-way valve

Control valve: Normally closed

Connecting thread: G3/4"-F

Design Data



Attribute	Value
d	9 mm
D	80 mm
G1	G3/4"-F
G2	G3/4"-F
G3	G3/4"-F
H	100 mm
H1	187.50 mm
H3	10 mm
L	206 mm
L2	43 mm
X1	45 mm
Y1	80 mm

Technical Data

Attribute	Value
Nominal size	20 mm
Control valve	Normally closed
Nominal flow rate	1200 l/min
Nominal flow rate	72 m³/h
Voltage DC	230V - AC
Weight	5.80 kg

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Solenoid valve

EMVO 20 230V-AC 3/2 NC


Part no.:10.05.01.00053

<https://www.schmalz.com/10.05.01.00053>

Product family

EMVO

Accessories



FAS 80x39 G3/4-AG

Part no.:10.05.01.00062

External diameter D: 80 mm

Length L: 39 mm

Thread G1: G3/4"-M

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi