

Vacuum hose (meter)

VSL 26-19 PVC-DS KL-TR

Part no.:10.07.09.00007

<https://www.schmalz.com/10.07.09.00007>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 26-19 PVC-DS KL-TR

Hose for vacuum and compressed-air systems



External diameter D: 26 mm

Internal diameter d: 19 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C

Design Data



Attribute	Value
d	19 mm
D	26 mm

Technical Data

Attribute	Value
Hose type	26-19
Pressure range (operating pressure)	-0.90 ... 5.00 bar
Operating temperature	-15 ... 65 °C
Bending radius min.	85 mm
Length max.	50 m
Weight/Meter	330 g/m
Weight/Meter	0.33 kg/m
Material hose	PVC with wire spiral

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum hose (meter)

VSL 26-19 PVC-DS KL-TR

Part no.:10.07.09.00007


<https://www.schmalz.com/10.07.09.00007>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSB 20-32 ST-VZ

Part no.:10.07.10.00003

Clamping range: 20.0 ... 32.0 mm

Material: Steel

Surface: galvanised



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



ST G1/2-AG 19 MS-V

Part no.:10.08.03.00163

Thread G1: G1/2"-M

Hose diameter (rec.) d: 19 mm

Material: Brass

Surface: nickel plated

Length L: 10 mm

Nominal diameter dn: 14.3 mm

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum hose (meter)

VSL 26-19 PVC-DS KL-TR

Part no...:10.07.09.00007

<https://www.schmalz.com/10.07.09.00007>



ST G3/4-AG 19 MS-V

Part no...:10.08.03.00165

Thread G1: G3/4"-M

Hose diameter (rec.) d: 19 mm

Material: Brass

Surface: nickel plated

Length L: 7.8 mm

Nominal diameter dn: 16 mm