

Vacuum hose (meter)

VSL 41-32 PVC-DS KL-TR

Part no.:10.07.09.00008

<https://www.schmalz.com/10.07.09.00008>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 41-32 PVC-DS KL-TR

Hose for vacuum and compressed-air systems



External diameter D: 41 mm

Internal diameter d: 32 mm

Length max.: 50 m


Material hose: PVC with wire spiral

Bending radius min.: 110 mm

Pressure range (operating pressure): -0.85 ... 4.00 bar

Operating temperature: -15 ... 65 °C

Design Data



Attribute	Value
d	32 mm
D	41 mm

Technical Data

Attribute	Value
Hose type	41-32
Pressure range (operating pressure)	-0.85 ... 4.00 bar
Operating temperature	-15 ... 65 °C
Bending radius min.	110 mm
Length max.	50 m
Weight/Meter	710 g/m
Weight/Meter	0.71 kg/m
Material hose	PVC with wire spiral

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum hose (meter)

VSL 41-32 PVC-DS KL-TR

Part no.:10.07.09.00008

<https://www.schmalz.com/10.07.09.00008>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSB 32-50 ST-VZ

Part no.:10.07.10.00004

Clamping range: 32.0 ... 50.0 mm

Material: Steel

Surface: galvanised



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



SSB 40-60 ST-VZ

Part no.:10.07.10.00005

Clamping range: 40.0 ... 60.0 mm

Material: Steel

Surface: galvanised

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum hose (meter)

VSL 41-32 PVC-DS KL-TR

Part no...:10.07.09.00008

<https://www.schmalz.com/10.07.09.00008>



ST G1-AG 32 MS-V

Part no...:10.08.03.00168

Thread G1: G1"-M

Hose diameter (rec.) d: 32 mm

Material: Brass

Surface: nickel plated

Length L: 10.5 mm

Nominal diameter dn: 26 mm



ST G1-1/4-AG 32 MS-V

Part no...:10.08.03.00169

Thread G1: G1-1/4"-M

Hose diameter (rec.) d: 32 mm

Material: Brass

Surface: nickel plated

Length L: 10.3 mm

Nominal diameter dn: 27.9 mm