

Hose sleeve

ST M5-AG 4 MS-V

Part no.:10.08.03.00152

<https://www.schmalz.com/10.08.03.00152>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST M5-AG 4 MS-V

Hose sleeve



Thread G1: M5-M

Hose diameter (rec.) d: 4 mm


Material: Brass

Surface: nickel plated

Length L: 3.3 mm

Nominal diameter dn: 2.2 mm

Design Data



Attribute	Value
dn	2.20 mm
D	4.40 mm
G1	M5-M
L	3.30 mm
L1	18.40 mm
LG1	4.40 mm
SW1	8 mm

Technical Data

Attribute	Value
Material	Brass
Weight	2 g

Accessories

Contact Schmalz


Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose sleeve

ST M5-AG 4 MS-V

Part no.:10.08.03.00152

<https://www.schmalz.com/10.08.03.00152>



VSL 6-4 PE BL

Part no.:10.07.09.00014

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 6-4 PTFE MI-TR

Part no.:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C



VSL 6-4 PU MI-TR

Part no.:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C