

Hose sleeve

ST G1/2-AG 9 MS-V

Part no.:10.08.03.00161

<https://www.schmalz.com/10.08.03.00161>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1/2-AG 9 MS-V

Hose sleeve



Thread G1: G1/2"-M

Hose diameter (rec.) d: 9 mm


Material: Brass

Surface: nickel plated

Length L: 6.1 mm

Nominal diameter dn: 7.5 mm

Design Data



Attribute	Value
dn	7.50 mm
D	8.60 mm
G1	G1/2"-M
L	6.10 mm
L1	45 mm
LG1	11.90 mm
SW1	24 mm

Technical Data

Attribute	Value
Material	Brass
Weight	50 g

Accessories

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose sleeve

ST G1/2-AG 9 MS-V

Part no...:10.08.03.00161

<https://www.schmalz.com/10.08.03.00161>



VSL 12-9 PE BL

Part no...:10.07.09.00050

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 12-9 PU MI-TR

Part no...:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C



VSL 15-9 PVC-G KL-TR

Part no...:10.07.09.00005

External diameter D: 15 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C