

Hose sleeve


ST G3/4-AG 13 MS-V

Part no.:10.08.03.00164

<https://www.schmalz.com/10.08.03.00164>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G3/4-AG 13 MS-V

Hose sleeve



Thread G1: G3/4"-M

Hose diameter (rec.) d: 13 mm


Material: Brass

Surface: nickel plated

Length L: 8 mm

Nominal diameter dn: 10.4 mm

Design Data



Attribute	Value
dn	10.40 mm
D	13.90 mm
G1	G3/4"-M
L	8 mm
L1	60 mm
LG1	16 mm
SW1	32 mm

Technical Data

Attribute	Value
Material	Brass
Weight	116 g

Accessories

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose sleeve

ST G3/4-AG 13 MS-V

Part no.:10.08.03.00164

<https://www.schmalz.com/10.08.03.00164>



VSL 19-13 PVC-DS KL-TR

Part no.:10.07.09.00016

External diameter D: 19 mm

Internal diameter d: 13 mm


Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C



VSL 21-12 PVC-G KL-TR

Part no.:10.07.09.00006

External diameter D: 21 mm

Internal diameter d: 12 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C