

Hose sleeve

ST G1-1/2-AG 38 MS-V

Part no.:10.08.03.00170

<https://www.schmalz.com/10.08.03.00170>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1-1/2-AG 38 MS-V

Hose sleeve



Thread G1: G1-1/2"-M

Hose diameter (rec.) d: 38 mm


Material: Brass

Surface: nickel plated

Length L: 12.2 mm

Nominal diameter dn: 29.9 mm

Design Data



Attribute	Value
dn	29.90 mm
D	38 mm
G1	G1-1/2"-M
L	12.20 mm
L1	64 mm
LG1	15.50 mm
SW1	50 mm

Technical Data

Attribute	Value
Material	Brass
Weight	400 g

Accessories

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose sleeve

ST G1-1/2-AG 38 MS-V

Part no.:10.08.03.00170

<https://www.schmalz.com/10.08.03.00170>



VSL 48-38 PU-DS-AS TR

Part no.:10.07.09.00031

External diameter D: 48 mm

Internal diameter d: 38 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 29 mm

Pressure range (operating pressure): -1.00 ... 3.21 bar

Operating temperature: -40 ... 90 °C



VSL 49-38 PU-DS-AS TR

Part no.:10.07.09.00052

External diameter D: 49 mm

Internal diameter d: 38 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 104 mm

Pressure range (operating pressure): -1.00 ... 4.47 bar

Operating temperature: -20 ... 90 °C



VSL 48-38 PVC-DS KL-TR

Part no.:10.07.09.00009

External diameter D: 48 mm

Internal diameter d: 38 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 120 mm

Pressure range (operating pressure): -0.88 ... 7.00 bar

Operating temperature: -15 ... 65 °C