

Flat suction cup (round)


SUF 35 HT1-60 SC050

Part no...:10.01.01.13994

<https://www.schmalz.com/10.01.01.13994>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 35 HT1-60 SC050

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 35

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Design Data



Attribute	Value
d1	17.20 mm
d	11 mm
Dk	23.30 mm
Dmax(S)	39.20 mm
Ds	35 mm
H	14.90 mm
H2	6.80 mm
H3	9.30 mm
Z (Stroke)	3.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	46 N
Pull-off force	46 N
Volume	2.40 cm ³
Curve radius (min) (convex)	40 mm
Size	35
Nipple family	SC050
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	5.50 g

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SUF 35 HT1-60 SC050

Part no.:10.01.01.13994

<https://www.schmalz.com/10.01.01.13994>

Product family

SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 050 G1/8-AG

Part no.:10.01.06.04250

Connection geometry: 050

Vacuum connection: G1/8"-M

Fitting length: 7.2 mm

Nominal diameter dn: 4.1 mm



SC 050 G1/8-IG

Part no.:10.01.06.04308

Connection geometry: 050

Vacuum connection: G1/8"-F

Fitting length: 14 mm

Nominal diameter dn: 6.1 mm