

Flat suction cup (round)

PFG 1 NBR-ESD-55 N001

Part no.:10.01.01.14345

<https://www.schmalz.com/10.01.01.14345>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 1 NBR-ESD-55 N001

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 1

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	0.80 mm
Dk	1.20 mm
Dmax(S)	1.20 mm
Ds	1 mm
H	1.60 mm
Z (Stroke)	0.10 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	0.03 N
Volume	0.00 cm ³
Curve radius (min) (convex)	2 mm
Size	1
Nipple family	N 001
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Weight	0 g

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

PFG 1 NBR-ESD-55 N001

Part no.:10.01.01.14345

<https://www.schmalz.com/10.01.01.14345>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N001 M3-AG DN40

Part no.:10.01.01.00315

Thread G1: M3-M

Length L1: 6 mm

Fitting length: 2 mm

Material: Aluminum