

Flexolink HD

FLK-HD G1/2-IG

Part no.:10.07.06.00242

<https://www.schmalz.com/10.07.06.00242>




Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > FLK-HD G1/2-IG

Flexible, reinforced suction cup mounting FLK-HD for adaption to sloping surfaces



Thread G1: G1/2"-F
Thread G2: M6-M
Operating temperature: -5 ... 130 °C

Design Data



Attribute	Value
L	41.60 mm
D	69 mm
dn	9 mm
d	6.40 mm
G1	G1/2"-F
LG1	14 mm
G2	M6-M
LG2	10.50 mm
SW1	24 mm
SW2	5 mm
Dmk	58.30 mm
W	7.50 °
Fitting length	41.60 mm