

Hose clamp

SSD 43-48 ST-VZ

Part no.:10.07.10.00020

<https://www.schmalz.com/10.07.10.00020>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSD 43-48 ST-VZ

Hose clamp for securing wire-reinforced hoses




Clamping range: 43.0 ... 48.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	43 mm
d2	48 mm
L	15 mm

Technical Data

Attribute	Value
Clamping range	43.0 ... 48.0 mm
Material	Steel
Weight	27 g
Product family	SSB / SSD

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose clamp

SSD 43-48 ST-VZ

Part no.:10.07.10.00020

<https://www.schmalz.com/10.07.10.00020>

Accessories



VSL 48-38 PU-DS-AS TR

Part no.:10.07.09.00031

External diameter D: 48 mm

Internal diameter d: 38 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 29 mm

Pressure range (operating pressure): -1.00 ... 3.21 bar

Operating temperature: -40 ... 90 °C



VSL 49-38 PU-DS-AS TR

Part no.:10.07.09.00052

External diameter D: 49 mm

Internal diameter d: 38 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 104 mm

Pressure range (operating pressure): -1.00 ... 4.47 bar

Operating temperature: -20 ... 90 °C



VSL 48-40 PVC-PS GR

Part no.:10.07.09.00011

External diameter D: 48 mm

Internal diameter d: 40 mm

Length max.: 50 m

Material hose: PVC with PVC-spiral

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.49 ... 1.00 bar

Operating temperature: -20 ... 70 °C

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi