

Hose clamp

SSD 65-70 ST-VZ

Part no.: 10.07.10.00098

<https://www.schmalz.com/10.07.10.00098>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSD 65-70 ST-VZ

Hose clamp for securing wire-reinforced hoses




Clamping range: 65.0 ... 70.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	65 mm
d2	70 mm
L	13 mm

Technical Data

Attribute	Value
Clamping range	65.0 ... 70.0 mm
Material	Steel
Weight	28.10 g
Product family	SSB / SSD

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose clamp

SSD 65-70 ST-VZ

Part no.:10.07.10.00098

<https://www.schmalz.com/10.07.10.00098>

Accessories



VSL 71-60 PU-DS-AS TR

Part no.:10.07.09.00034

External diameter D: 71 mm

Internal diameter d: 60 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 40 mm

Pressure range (operating pressure): -0.69 ... 2.09 bar

Operating temperature: -40 ... 90 °C



VSL 71-60 PU-DS-AS TR

Part no.:10.07.09.00065

External diameter D: 71 mm

Internal diameter d: 60 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 156 mm

Pressure range (operating pressure): -1.00 ... 2.92 bar

Operating temperature: -40 ... 90 °C



VSL 71-60 PVC-DS GR

Part no.:10.07.09.00012

External diameter D: 71 mm

Internal diameter d: 60 mm

Length max.: 25 m

Material hose: PVC with wire spiral

Bending radius min.: 110 mm

Pressure range (operating pressure): -0.73 ... 1.27 bar

Operating temperature: -20 ... 70 °C