

Hose sleeve

ST G1-AG 25 MS-V

Part no.:10.08.03.00167

<https://www.schmalz.com/10.08.03.00167>

Home > Accessories for Screw Unions > ST G1-AG 25 MS-V

Hose sleeve



Thread G1: G1"-M

Hose diameter (rec.) d: 25 mm


Material: Brass

Surface: nickel plated

Length L: 10.1 mm

Nominal diameter dn: 22 mm

Design Data



Attribute	Value
dn	22 mm
D	25 mm
G1	G1"-M
L	10.10 mm
L1	62 mm
LG1	15.80 mm
SW1	36 mm

Technical Data

Attribute	Value
Material	Brass
Weight	159 g

Accessories

Contact Schmalz


Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose sleeve

ST G1-AG 25 MS-V

Part no...:10.08.03.00167

<https://www.schmalz.com/10.08.03.00167>



VSL 32-25 PU-DS-AS TR

Part no...:10.07.09.00051

External diameter D: 32 mm

Internal diameter d: 25 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 20 mm

Pressure range (operating pressure): -1.00 ... 3.86 bar

Operating temperature: -40 ... 90 °C



VSL 33-25 PVC-DS KL-TR

Part no...:10.07.09.00041

External diameter D: 33 mm

Internal diameter d: 25 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 95 mm

Pressure range (operating pressure): -0.85 ... 4.00 bar

Operating temperature: -15 ... 65 °C