

Vacuum hose (meter)


VSL 32-25 PU-DS-AS TR

Part no.:10.07.09.00051

<https://www.schmalz.com/10.07.09.00051>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 32-25 PU-DS-AS TR

Hose for vacuum and compressed-air systems



External diameter D: 32 mm

Internal diameter d: 25 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 20 mm

Pressure range (operating pressure): -1.00 ... 3.86 bar

Operating temperature: -40 ... 90 °C

Design Data



Attribute	Value
d	25 mm
D	32 mm

Technical Data

Attribute	Value
Hose type	32-25
Pressure range (operating pressure)	-1.00 ... 3.86 bar
Operating temperature	-40 ... 90 °C
Bending radius min.	20 mm
Length max.	20 m
Weight/Meter	280 g/m
Weight/Meter	0.28 kg/m
Material hose	PU, wire spiral, antistatic

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum hose (meter)

VSL 32-25 PU-DS-AS TR

Part no.:10.07.09.00051

<https://www.schmalz.com/10.07.09.00051>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSB 32-50 ST-VZ

Part no.:10.07.10.00004

Clamping range: 32.0 ... 50.0 mm

Material: Steel

Surface: galvanised



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



ST G1-AG 25 MS-V

Part no.:10.08.03.00167

Thread G1: G1"-M

Hose diameter (rec.) d: 25 mm

Material: Brass

Surface: nickel plated

Length L: 10.1 mm

Nominal diameter dn: 22 mm

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum hose (meter)

VSL 32-25 PU-DS-AS TR

Part no...:10.07.09.00051

<https://www.schmalz.com/10.07.09.00051>



ST G3/4-AG 25 MS-V

Part no...:10.08.03.00166

Thread G1: G3/4"-M

Hose diameter (rec.) d: 25 mm

Material: Brass

Surface: nickel plated

Length L: 8.5 mm

Nominal diameter dn: 18.5 mm