

## Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Manual Work > Multi-Clamp System VC-M / VC-M-V > VC-M-BV 265x170x209

### Turning and slewing device Base



Length L: 265 mm

Width B: 170 mm

Height H: 209 mm

### Design Data



| Attribute | Value  |
|-----------|--------|
| B         | 170 mm |
| H         | 209 mm |
| L         | 265 mm |

### Technical Data

| Attribute | Value   |
|-----------|---------|
| Weight    | 7.34 kg |

### Accessories

#### Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | [schmalz@schmalz.fi](mailto:schmalz@schmalz.fi)

## Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>



**DI-PROF 8x10.5 MOS EPDM-15**

Part no...:10.01.12.02056



**FU 5 3/2 -**

Part no...:10.01.12.02055

Nominal size: 5 mm

Thread G1: G1/4"-F



**REIB-INS 8.1x18 VC-M**

Part no...:10.01.12.02000

Construction use: Multi-Clamp

## Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | [schmalz@schmalz.fi](mailto:schmalz@schmalz.fi)

## Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>



### VC-M-PU 4 110V-AC

Part no...:10.01.12.02051

Current type: 1-phase AC 110V

Max. vacuum: -850 mbar

Nominal size: 9 mm



### VC-M-PU 4 230V-AC

Part no...:10.01.12.02040

Current type: 1-phase AC 230V

Max. vacuum: -850 mbar

Nominal size: 9 mm



### VC-M-SPV 160x160x30

Part no...:10.01.12.01853

Length L: 160 mm

Width B: 160 mm

Height H: 30 mm

Suction rate: 3 m<sup>3</sup>/h

## Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>



### VC-M-SPV 200x55

Part no...:10.01.12.02009

Length L: 200 mm

Width B: 55 mm



### VC-M-SPV 210

Part no...:10.01.12.02008

External diameter D: 210 mm



### VC-M-SPV 300x100

Part no...:10.01.12.02053

Length L: 300 mm

Width B: 100 mm

## Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | [schmalz@schmalz.fi](mailto:schmalz@schmalz.fi)

## Multi-Base

VC-M-BV 265x170x209

Part no...:10.01.12.02050

<https://www.schmalz.com/10.01.12.02050>



### ZUB VC-M-V

Part no...:10.01.12.02054

Construction use: Multi-Clamp