

Cup

ISCUP Cup 4 100x100x30

Part no...:10.01.15.00403

<https://www.schmalz.com/10.01.15.00403>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP Cup 4 100x100x30

Suction cup for Innospann




Dimensions (LxB): 100 x 100

Length L: 100 mm

Width B: 100 mm

Height H: 30 mm

Design Data



Attribute	Value
B	100 mm
d	60 mm
H	30 mm
L	100 mm

Technical Data

Attribute	Value
Weight	0.21 kg

Spare parts

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Cup

ISCUP Cup 4 100x100x30

Part no...:10.01.15.00403

<https://www.schmalz.com/10.01.15.00403>



DI-PROF 4x10 MOS EPDM HR

Part no...:10.01.15.00062


Width B: 4 mm

Height H: 10 mm

Sealing material: EPDM

Material type: Foam rubber

Form: half-round



ISDR 100x100x12 Cup 4


Part no...:10.01.15.00404

Width B: 100 mm

Height H: 12 mm

Length L: 100 mm

Type: Cup 4



ISRPL 86x86x8.7 NBR-55 d5

Part no...:10.01.15.00402

Width B: 86 mm

Internal diameter d: 5 mm

Height H: 8.7 mm

Length L: 86 mm

Suction cup material: Nitrile rubber NBR-55

Type: CUP 100

Cup

ISCUP Cup 4 100x100x30

Part no...:10.01.15.00403

<https://www.schmalz.com/10.01.15.00403>



O-RING 48x2 CR-70

Part no...:10.07.08.00468