

Vacuum module

VEE-QCMV HV 2 07 13 SD

Part no...:10.01.36.00206

<https://www.schmalz.com/10.01.36.00206>

Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Vacuum End Effectors VEE > Vacuum Modules VEE-QCMV > VEE-QCMV HV 2 07 13 SD

VEE vacuum module with integrated ejector module ecoPump SEP




Shape: High Vacuum

Number of stages: 2

Nozzle size: 0.7 mm

Add. function: Silencer

Design Data



Attribute	Value
B	55 mm
d	6 mm
D	25.40 mm
Dmk	46 mm
G1	G1/8"-F
G2	M4-M
H	37.90 mm
H1	53 mm
L	133.10 mm
L2	89 mm
LG2	7.60 mm

Accessories

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum module

VEE-QCMV HV 2 07 13 SD

Part no...:10.01.36.00206

<https://www.schmalz.com/10.01.36.00206>



EMV 1.5 24V-DC 3/2 NC K-2P

Part no...:10.05.01.00288

Nominal size: 1.5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Normally closed

Connecting thread: M5-M

Pressure range (operating pressure): 3.5 ... 7.0 bar

Interface electrical connection: Cable, 2 pol



FLAN-PL 55x7.5-AB1

Part no...:10.01.30.00015

External diameter D: 55 mm

Length L: 7.5 mm

Size: AB1



FLAN-PL 55x7.5-EL1

Part no...:10.01.30.00208

External diameter D: 55 mm

Length L: 7.5 mm

Size: EL1

Vacuum module

VEE-QCMV HV 2 07 13 SD

Part no...:10.01.36.00206

<https://www.schmalz.com/10.01.36.00206>



FLAN-PL 55x9.5-JP1

Part no...:10.01.30.00194

External diameter D: 55 mm

Length L: 9.5 mm

Size: JP1

Thread G1: G3/8"-F



FLAN-PL 63x10.5-AD1

Part no...:10.01.30.00016

External diameter D: 63 mm

Length L: 10.5 mm

Size: AD1



FLAN-PL 63x11.5-UNI

Part no...:10.01.30.00017

External diameter D: 63 mm

Length L: 11.5 mm

Size: UNI

Vacuum module

VEE-QCMV HV 2 07 13 SD

Part no...:10.01.36.00206

<https://www.schmalz.com/10.01.36.00206>



FLAN-PL 80x12-ST1

Part no...:10.01.30.00167

External diameter D: 80 mm

Length L: 12 mm

Size: ST1



RFBP 50 50 BA SPB2

Part no...:10.01.45.00096

Length L: 50 mm

Width B: 50 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2



RFBP 100 58 BA SPB2

Part no...:10.01.45.00091

Length L: 100 mm

Width B: 58 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2

Vacuum module

VEE-QCMV HV 2 07 13 SD

Part no...:10.01.36.00206

<https://www.schmalz.com/10.01.36.00206>



RFBP 100 58 BA O10

Part no...:10.01.45.00092

Length L: 100 mm

Width B: 58 mm

Connection: Bayonet connection

Material type: Foam O, Height 10 mm



RFBP 120 120 BA SPB2

Part no...:10.01.45.00085

Length L: 120 mm

Width B: 120 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2



RFBP 120 120 BA O10

Part no...:10.01.45.00086

Length L: 120 mm

Width B: 120 mm

Connection: Bayonet connection

Material type: Foam O, Height 10 mm

Spare parts

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum module

VEE-QCMV HV 2 07 13 SD

Part no...:10.01.36.00206

<https://www.schmalz.com/10.01.36.00206>



SD 16.5x51.5 SHC 13

Part no...:10.02.01.01498

External diameter D: 16.5 mm

Length L: 51.5 mm

Construction use: Schmalz Holder Cap

Size: 13



SEP HV 2 07 13

Part no...:10.02.01.01394

Shape: High Vacuum

Number of stages: 2

Nozzle size: 0.7 mm

Hole diameter: 13 mm

Degree of evacuation: 85 %

Pressure range (operating pressure): 2.0 ... 6.0 bar

Pressure optimal: 4 bar

Suction rate (max.): 42.5 l/min

Air consumption suction: 23.5 l/min



SHC 2 13 SD

Part no...:10.02.01.01426

Number of stages: 2

Hole diameter: 13 mm

Length L: 70 mm

Thread G1: M16x1-M