

Hose sleeve

ST G1/2-AG 19 MS-V

Part no.:10.08.03.00163

<https://www.schmalz.com/10.08.03.00163>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1/2-AG 19 MS-V

Hose sleeve



Thread G1: G1/2"-M

Hose diameter (rec.) d: 19 mm


Material: Brass

Surface: nickel plated

Length L: 10 mm

Nominal diameter dn: 14.3 mm

Design Data



Attribute	Value
dn	14.30 mm
D	19 mm
G1	G1/2"-M
L	10 mm
L1	58 mm
LG1	12 mm
SW1	24 mm

Technical Data

Attribute	Value
Material	Brass
Weight	85 g

Accessories

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose sleeve

ST G1/2-AG 19 MS-V

Part no...:10.08.03.00163

<https://www.schmalz.com/10.08.03.00163>



VSL 26-19 PVC-DS KL-TR

Part no...:10.07.09.00007

External diameter D: 26 mm

Internal diameter d: 19 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi