

Hose clamp

SSB 10-16 ST-VZ

Part no.:10.07.10.00001

<https://www.schmalz.com/10.07.10.00001>

Home > Vacuum Lifters and Crane Systems > Vacuum Tube Lifters Jumbo > Spare Parts Vacuum Tube Lifters Jumbo > Spare and Wear Parts Vacuum Tube Lifters JumboFlex > SSB 10-16 ST-VZ

Hose clamp for securing smooth hoses




Clamping range: 10.0 ... 16.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	10 mm
d2	16 mm
L	9 mm

Technical Data

Attribute	Value
Clamping range	10.0 ... 16.0 mm
Material	Steel
Weight	12 g
Product family	SSB / SSD

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose clamp

SSB 10-16 ST-VZ

Part no.:10.07.10.00001

<https://www.schmalz.com/10.07.10.00001>

Accessories



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



VSL 10-7 PE MI-TR

Part no.:10.07.09.00083

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PE

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -30 ... 70 °C



VSL 10-7 PU MI-TR

Part no.:10.07.09.00084

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 85 °C

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Hose clamp

SSB 10-16 ST-VZ

Part no.:10.07.10.00001

<https://www.schmalz.com/10.07.10.00001>



VSL 12-9 PE BL

Part no.:10.07.09.00050

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 12-9 PU MI-TR

Part no.:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C



VSL 14-11 PU MI-TR

Part no.:10.07.09.00038

External diameter D: 14 mm

Internal diameter d: 11 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 100 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Hose clamp

SSB 10-16 ST-VZ

Part no...:10.07.10.00001

<https://www.schmalz.com/10.07.10.00001>



VSL 15-9 PVC-G KL-TR

Part no...:10.07.09.00005

External diameter D: 15 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C