

Suspension, rigid

FST-STARR 75 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.07011

<https://www.schmalz.com/10.01.10.07011>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Suspension Rigid/Flexible Set > Suspension Rigid FST-STARR > FST-STARR 75 HD1 G1/2-AG G3/8-IG

Spring plunger with both-way damping and height compensation, heavy-duty




Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section

Design Data



Attribute	Value
B	75 mm
G1	G3/8"-F
G2	G1/2"-M
H	238.60 mm
H1	200 mm
H2	20 mm
L	41 mm
LG1	13 mm
LG2	10.50 mm
Z (Stroke)	75 mm

Technical Data

Attribute	Value
Spring rate	1.07 N/mm
Weight	1300 g
Product family	FST-STARR

Accessories

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Suspension, rigid

FST-STARR 75 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.07011

<https://www.schmalz.com/10.01.10.07011>



FLAN-PL 120x85x10 ST FLGR

Part no...:10.01.10.05701

Length L: 120 mm

Width B: 85 mm

Height H: 10 mm

Material: Steel

Construction use: Vacuum area gripping system



FLK G1/2-IG G1/2-AG

Part no...:10.01.03.00175

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C



FLK G1/2-IG G1/2-AG V

Part no...:10.01.03.00207

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C

Shape mounting elements: Reinforced