

Bellows suction cup (round)

FG 20 NBR-ESD-55 N062

Part no.:10.01.06.04235

<https://www.schmalz.com/10.01.06.04235>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 20 NBR-ESD-55 N062

Bellows suction cup (round) for very uneven workpieces




Size: 20

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Number of folds: 2.5

Design Data



Attribute	Value
d	4.50 mm
d2	10.50 mm
D1	20 mm
Dk	10 mm
Dmax(S)	21 mm
Ds	20 mm
H	22.10 mm
H2	3.80 mm
H3	9 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	5.20 N
Pull-off force	12.10 N
Volume	2.30 cm ³
Curve radius (min) (convex)	10 mm
Size	20
Number of folds	2.50
Suction cup material	Nitrile rubber NBR-ESD

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cup (round)

FG 20 NBR-ESD-55 N062

Part no.:10.01.06.04235

<https://www.schmalz.com/10.01.06.04235>

Material hardness [Shore A]

55 Shore A

Weight

2.40 g

Product family

FG

Accessories



SA-NIP N062 M5-AG DN250

Part no.:10.01.06.05668

Thread G1: M5-M

Length L1: 15.9 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum



SA-NIP N062 G1/8-IG DN350

Part no.:10.01.06.05669

Thread G1: G1/8"-F

Length L1: 17.9 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N062 G1/8-AG DN350

Part no.:10.01.06.05670

Thread G1: G1/8"-M

Length L1: 19.4 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cup (round)

FG 20 NBR-ESD-55 N062

Part no...:10.01.06.04235

<https://www.schmalz.com/10.01.06.04235>
