

Flat suction cup (oval)

SGO 15x5 NBR-ESD-55 N021

Part no...:10.01.05.00931

<https://www.schmalz.com/10.01.05.00931>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 15x5 NBR-ESD-55 N021


Flat suction cup (oval) for narrow or curved workpieces



Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
Bmax(S)	5.50 mm
Bs	4.60 mm
d	4.50 mm
d1	6 mm
dn	1.20 mm
Dk	8.50 mm
Lmax(S)	15.50 mm
Ls	14.60 mm
H	12 mm
H2	3 mm
H3	5.50 mm
Z (Stroke)	0.70 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	3.10 N
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Weight	0.40 g
Product family	SGO

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (oval)

SGO 15x5 NBR-ESD-55 N021

Part no...:10.01.05.00931

<https://www.schmalz.com/10.01.05.00931>
