

Solenoid valve

EMVP 5 24V-DC 3/2 NC

Part no...:10.05.02.00162

<https://www.schmalz.com/10.05.02.00162>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMVP > EMVP 5 24V-DC 3/2 NC

Solenoid valve EMVP for vacuum, pneumatic pilot control



Nominal size: 5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Normally closed


Connecting thread: G1/8"-F

Pressure range (operating pressure): -0.95 ... 0.00 bar

Nominal flow rate: 3 m³/h

Weight: 0.11 kg

Design Data



Attribute	Value
B	15 mm
B2	15 mm
d	4.30 mm
G1	G1/8"-F
G2	G1/8"-F
G3	G1/8"-F
G4	M5-F
H	88.40 mm
H2	19.50 mm
H3	12 mm
H4	27 mm
L	32 mm
L1	37 mm
X1	23 mm
Y1	15 mm

Technical Data

Attribute	Value
Nominal size	5 mm
Nominal flow rate	3 m ³ /h

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Solenoid valve


EMVP 5 24V-DC 3/2 NC

Part no...:10.05.02.00162

<https://www.schmalz.com/10.05.02.00162>

Control valve	Normally closed
Nominal flow rate	50 l/min
Power consumption DC	1 W
Voltage DC	24V - DC
Closing time	19 ms
Weight	0.11 kg
Product family	EMVP

Accessories



ASK B-Form-C 5000 K-3P

Part no...:21.04.06.00084

Electrical connection: Fem connect Form C

Cable length: 5,000 mm

Material hose: PVC cable