

Feed ejector

SEC-400

Part no.:10.02.01.00080

<https://www.schmalz.com/10.02.01.00080>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Feed Ejectors > Feed Ejectors SEC > SEC-400


Powerful ejector for very porous parts



Nozzle size: 40 mm

Suction rate (max.): 135 m³/h

Design Data



Attribute	Value
D	84 mm
D1	75 mm
D2	52 mm
G2	G3/8"-F
G3	M4-F
L	35 mm
L1	95 mm
LG3	14 mm
X1	72 mm

Technical Data

Attribute	Value
Max. vacuum	-25 mbar
Suction rate (max.)	2250 l/min
Suction rate (max.)	135 m ³ /h
Air consumption suction	500 l/min
Air consumption suction	26.70 m ³ /h
Pressure range (operating pressure)	2.0 ... 6.0 bar
Operating temperature	-20 ... 80 °C
Weight	0.53 kg
Max. vacuum	-0.74 inHg

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Feed ejector

SEC-400

Part no...:10.02.01.00080

<https://www.schmalz.com/10.02.01.00080>

Suction rate (max.)	79.46 cfm
Air consumption suction	17.66 cfm
Pressure range (operating pressure)	29.0 ... 87.0
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)
