

## Feed ejector

SEC-750

Part no.:10.02.01.00081

<https://www.schmalz.com/10.02.01.00081>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Feed Ejectors > Feed Ejectors SEC > SEC-750


### Powerful ejector for very porous parts



Nozzle size: 75 mm

Suction rate (max.): 518.4 m³/h

### Design Data



| Attribute | Value   |
|-----------|---------|
| D         | 140 mm  |
| D1        | 125 mm  |
| D2        | 100 mm  |
| G2        | G1/2"-F |
| G3        | M6-F    |
| L         | 65 mm   |
| L1        | 180 mm  |
| LG3       | 6 mm    |
| X1        | 126 mm  |

### Technical Data

| Attribute                           | Value           |
|-------------------------------------|-----------------|
| Max. vacuum                         | -5 mbar         |
| Suction rate (max.)                 | 8640 l/min      |
| Suction rate (max.)                 | 518.40 m³/h     |
| Air consumption suction             | 770 l/min       |
| Air consumption suction             | 46.20 m³/h      |
| Pressure range (operating pressure) | 2.0 ... 6.0 bar |
| Operating temperature               | -20 ... 80 °C   |
| Weight                              | 2.35 kg         |
| Max. vacuum                         | -0.15 inHg      |

### Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | [schmalz@schmalz.fr](mailto:schmalz@schmalz.fr)

## Feed ejector

SEC-750

Part no.:10.02.01.00081

<https://www.schmalz.com/10.02.01.00081>

|                                     |               |
|-------------------------------------|---------------|
| Suction rate (max.)                 | 305.11 cfm    |
| Air consumption suction             | 27.19 cfm     |
| Pressure range (operating pressure) | 29.0 ... 87.0 |
| Product family                      | SEC           |

Note: Air consumption: At optimal operating pressure (4,5 bar)

---