

## Plug union, T

STV-T M5-AG 4

Part no.:10.09.02.00038

<https://www.schmalz.com/10.09.02.00038>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-T M5-AG 4

### Push-in Fitting, T



Thread G1: M5-M


Hose diameter: 4 mm

Material: Brass

Operating temperature: °C

Length L: 34 mm

### Design Data



| Attribute | Value   |
|-----------|---------|
| d         | 4 mm    |
| G1        | M5-M    |
| dn        | 2 mm    |
| D1        | 8.70 mm |
| H         | 9.60 mm |
| H1        | 14 mm   |
| L         | 34 mm   |
| LG1       | 4.50 mm |
| SW1       | 8 mm    |

### Technical Data

| Attribute                           | Value            |
|-------------------------------------|------------------|
| Hose type                           | Hose D = 4 d = 2 |
| Hose type                           | 4-2              |
| Material                            | Brass            |
| Pressure range (operating pressure) | bar              |
| Operating temperature               | °C               |
| Weight                              | 14.20 g          |
| Product family                      | STV              |

### Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | [schmalz@schmalz.fr](mailto:schmalz@schmalz.fr)

## Plug union, T

STV-T M5-AG 4

Part no.:10.09.02.00038

<https://www.schmalz.com/10.09.02.00038>

### Accessories



#### VSL 4-2 PE BL

Part no.:10.07.09.00013

External diameter D: 4 mm

Internal diameter d: 2 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



#### VSL 4-2 PU MI-TR

Part no.:10.07.09.00001

External diameter D: 4 mm

Internal diameter d: 2 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 20 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 60 °C



#### VSL 4-2.7 PA MI-TR

Part no.:10.07.09.00063

External diameter D: 4 mm

Internal diameter d: 2.7 mm

Length max.: 50 m

Material hose: PA

Bending radius min.: 30 mm

Pressure range (operating pressure): -0.95 ... 20.00 bar

Operating temperature: -40 ... 90 °C

### Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | [schmalz@schmalz.fr](mailto:schmalz@schmalz.fr)