

Plug union, T

STV-T G1/8-AG 4

Part no.:10.09.02.00039

<https://www.schmalz.com/10.09.02.00039>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-T G1/8-AG 4

Push-in Fitting, T



Thread G1: G1/8"-M


Hose diameter: 4 mm

Material: Brass

Operating temperature: °C

Length L: 32.5 mm

Design Data



Attribute	Value
d	4 mm
G1	G1/8"-M
dn	3 mm
D1	8.70 mm
H	11.70 mm
H1	16 mm
L	32.50 mm
LG1	5.50 mm
SW1	13 mm

Technical Data

Attribute	Value
Hose type	Hose D = 4 d = 2
Hose type	4-2
Material	Brass
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	19.30 g
Product family	STV

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Plug union, T

STV-T G1/8-AG 4

Part no.:10.09.02.00039

<https://www.schmalz.com/10.09.02.00039>

Accessories



VSL 4-2 PE BL

Part no.:10.07.09.00013

External diameter D: 4 mm

Internal diameter d: 2 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 4-2 PU MI-TR

Part no.:10.07.09.00001

External diameter D: 4 mm

Internal diameter d: 2 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 20 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 60 °C



VSL 4-2.7 PA MI-TR

Part no.:10.07.09.00063

External diameter D: 4 mm

Internal diameter d: 2.7 mm

Length max.: 50 m

Material hose: PA

Bending radius min.: 30 mm

Pressure range (operating pressure): -0.95 ... 20.00 bar

Operating temperature: -40 ... 90 °C

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr